

# ALPHA

3470UER100P62 TFR

EAN 4031582485479



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

|                      |           |
|----------------------|-----------|
| Roll Performance     | ● ● ● ● ○ |
| Movement noise       | ● ● ● ● ● |
| Attrition            | ● ● ● ● ○ |
| Corrosion resistance | ● ● ● ● ○ |

## CORE ATTRIBUTES

|                             |                               |
|-----------------------------|-------------------------------|
| Product name                | Alpha                         |
| Type                        | Swivel caster                 |
| Standard                    | EN12532 - Transport Equipment |
| Load capacity at 2.5 mph    | 352.74 lb                     |
| Electric conductive         | no                            |
| Stainless                   | no                            |
| Load capacity Static        | 705.48 lb                     |
| Temperature range (Minimum) | -4 °F                         |
| Temperature range (Maximum) | 176 °F                        |
| Overall height              | 5.04 in                       |
| Overall weight              | 1.88 lb                       |

## HOUSING

|                     |                    |
|---------------------|--------------------|
| Housing Material    | Steel sheet, heavy |
| Fork shape          | Broad              |
| Swivel bearing      | Two ball races     |
| Housing Color       | Blue passivated    |
| Offset              | 1.61 in            |
| Swivel radius       | 3.54 in            |
| Swivel interference | 7.09 in            |

## WHEEL

|                       |                                 |
|-----------------------|---------------------------------|
| Tread hardness        | soft                            |
| Body material         | Polyamide                       |
| Tread material        | Elastic tire, black, vulcanized |
| Bearing               | Roller bearing                  |
| Axle                  | Screwed with nut                |
| Threadguards          | Without threadguard             |
| Diameter              | 3.94 in                         |
| Tread width           | 1.34 in                         |
| Hardness of tread (A) | 64 Shore A                      |

## FITTING

|                             |                   |
|-----------------------------|-------------------|
| Fitting type                | Rectangular plate |
| Plate length                | 4.13 in           |
| Plate width                 | 3.15 in           |
| Plate hole length (Minimum) | 3.03 in           |
| Plate hole length (Maximum) | 3.15 in           |
| Plate hole width (Maximum)  | 2.36 in           |
| Plate hole diameter         | 0.35 in           |

# ALPHA

3470UER100P62 TFR



EAN 4031582485479



BETTER MOBILITY. BETTER LIFE.

## Product Drawings

3470U00100P62-neu



Platte 3470-080P62-105x80

