

STYLEA

5920UOI065L51-11 DOM23x43,6 ALU

EAN 4031582335897



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll Performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ●
Corrosion resistance	● ● ● ● ○

CORE ATTRIBUTES

Product name	Stylea
Type	Swivel caster
Standard	EN12528 - Furniture Castors
Load capacity at 1.8 mph	110.23 lb
Electric conductive	no
Stainless	no
Load capacity Static	220.46 lb
Temperature range (Minimum)	14 °F
Temperature range (Maximum)	104 °F
Overall height	3.6 in
Overall width	1.81 in

HOUSING

Housing Material	Polyamide
Fork shape	Twin wheel housing
Swivel bearing	Stem, swiveling
Swivel radius	2.09 in
Swivel interference	4.17 in
Dome diameter	0.91 in

WHEEL

Body material	Polyamide
Tread material	Identical with wheel body
Bearing	Plain bearing with spacer tube
Axle	Riveted
Threadguards	Without threadguard
Diameter	2.56 in
Tread width	0.28 in

FITTING

Fitting type	Blind hole for B10 fitting
Bolt hole diameter	0.43 in

STYLEA

5920UOI065L51-11 DOM23x43,6 ALU

EAN 4031582335897



BETTER MOBILITY. BETTER LIFE.

Product Drawings

