

PRODUCT INFORMATION

MAXTECH

UAD200x50-Ø20 HL58 red

EAN 4031582419337



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

| | |
|-----------------------|---------------------------|
| Body material | Polyamide |
| Tread Material Mix | Polyurethane, injected |
| Bearing | Roller bearing, stainless |
| Diameter | 200 mm |
| Tread width | 50 mm |
| Axle Hole Diameter | 20 mm |
| Hub Length | 58 mm |
| Hardness of tread (D) | 42 Shore D |

PERFORMANCE

| | |
|----------------------|--------|
| Roll Performance | ●●●○○ |
| Movement Noise | ●●●○○ |
| Attrition | ●●●●○○ |
| Corrosion Resistance | ●●●○○ |

CORE ATTRIBUTES

| | |
|-----------------------------|-------------------------------|
| Product Name | Maxtech |
| Type | Wheel |
| Standard | EN12532 - Transport Equipment |
| Load capacity at 4 km/h | 500 kg |
| Electric Conductive | No |
| Stainless | No |
| Load capacity Static | 1000 kg |
| Temperature range (Minimum) | -40 °C |
| Temperature range (Maximum) | 80 °C |
| Overall weight | 0.91 kg |

MAXTECH

UAD200x50-Ø20 HL58 red

EAN 4031582419337



BETTER MOBILITY. BETTER LIFE.

Product Drawings

