

# ELASTECH

IFP300x55-Ø25

EAN 4031582366310



Image may differ from the original product

### PERFORMANCE

|                      |             |
|----------------------|-------------|
| Roll Performance     | ● ● ● ● ○ ○ |
| Movement Noise       | ● ● ● ● ○ ○ |
| Attrition            | ● ● ● ● ○ ○ |
| Corrosion Resistance | ● ● ● ● ○ ○ |

### CORE ATTRIBUTES


|                             |                               |
|-----------------------------|-------------------------------|
| Product Name                | Elastech                      |
| Type                        | Wheel                         |
| Standard                    | EN12532 - Transport Equipment |
| Load capacity at 4 km/h     | 600 kg                        |
| Load capacity at 6 km/h     | 480 kg                        |
| Electric Conductive         | No                            |
| Stainless                   | No                            |
| Load capacity Static        | 1200 kg                       |
| Temperature range (Minimum) | -20 °C                        |
| Temperature range (Maximum) | 85 °C                         |



BETTER MOBILITY. BETTER LIFE.

### WHEEL

|                       |                                       |
|-----------------------|---------------------------------------|
| Tread hardness        | soft                                  |
| Body material         | Aluminium                             |
| Tread Material Mix    | Elastic tire, non-marking, vulcanized |
| Bearing               | Precision ball bearing                |
| Threadguards          | Without threadguard                   |
| Diameter              | 300 mm                                |
| Tread width           | 55 mm                                 |
| Axle Hole Diameter    | 25 mm                                 |
| Hub Length            | 60 mm                                 |
| Hardness of tread (A) | 68 Shore A                            |




PRODUCT INFORMATION

**ELASTECH**

IFP300x55-Ø25

EAN 4031582366810



BETTER MOBILITY. BETTER LIFE.