

ZETA

4688ITP200P63

EAN 4031582030525
Order number 00803930



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

| | |
|----------------------|-------|
| Roll performance | ●●●○○ |
| Movement noise | ●●●●○ |
| Attrition | ●●●●○ |
| Corrosion resistance | ●●●○○ |

CORE ATTRIBUTES

| | |
|-----------------------------|-------------------------------|
| Product name | Zeta |
| Housing type | Fixed castor |
| Standard | EN12532 - Transport Equipment |
| Load capacity at 4 km/h | 800 kg |
| Load capacity at 6 km/h | 640 kg |
| Load capacity Static | 1600 kg |
| Temperature range (Minimum) | -10 °C |
| Temperature range (Maximum) | 60 °C |
| Overall height | 240 mm |
| Overall width | 117 mm |
| Overall weight | 2.644 kg |

WHEEL

| | |
|-----------------------|------------------------|
| Body material | Aluminium |
| Tread material | Polyurethane, casted |
| Bearing | Precision ball bearing |
| Axle | Screwed with nut |
| Wheel color | Honey yellow (RAL1005) |
| Threadguards | Without threadguard |
| Diameter | 200 mm |
| Tread width | 50 mm |
| Body width | 50 mm |
| Hardness of tread (A) | 92 Shore A |
| Hardness of tread (D) | 42 Shore D |

HOUSING

| | |
|------------|-------------------------|
| Material | Steel sheet, very heavy |
| Fork shape | Broad, reinforced |
| Colour | Blue passivated |

FITTING

| | |
|-----------------------------|-------------------|
| Fitting type | Rectangular plate |
| Plate length | 137 mm |
| Plate width | 117 mm |
| Plate hole length (Minimum) | 75 mm |
| Plate hole length (Maximum) | 80 mm |
| Plate hole width (Minimum) | 75 mm |
| Plate hole width (Maximum) | 105 mm |
| Plate hole diameter | 11 mm |

ZETA

4688ITP200P63

EAN 4031582030525
Order number 00803930



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

