

ALPHA

3477UOO080P30-13 TFR

EAN 4031582485561



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ●
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Alpha
Housing type	Swivel castor with total lock
Standard	EN12532 - Transport Equipment
Load capacity at 2.5 mph	330.69 lb
Load capacity Static	661.39 lb
Temperature range (Minimum)	-4 °F
Temperature range (Maximum)	140 °F
Overall height	4.25 in
Overall weight	1.92 lb

WHEEL

Body material	Polyamide
Tread material	Identical with wheel body
Bearing	Plain bearing
Axle	Screwed with nut
Threadguards	Without threadguard
Diameter	3.15 in
Tread width	1.18 in
Hardness of tread (D)	75 Shore D

HOUSING

Material	Steel sheet, heavy
Fork shape	Broad
Swivel bearing	Two ball races
Offset	1.75 in
Swivel radius	4.76 in
Swivel interference	9.53 in

FITTING

Fitting type	Bolt hole
Bolt hole diameter	0.51 in

ALPHA

3477UOO080P30-13 TFR

EAN 4031582485561



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

