

AGILA CARE

2476DIK100R26-28S45

EAN 4031582301700



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

| | |
|----------------------|-----------|
| Roll performance | ● ● ● ○ ○ |
| Movement noise | ● ● ● ○ ○ |
| Attrition | ● ● ● ○ ○ |
| Corrosion resistance | ● ● ● ○ ○ |

CORE ATTRIBUTES

| | |
|-----------------------------|--|
| Product name | Agila care |
| Housing type | Swivel castor with central, total lock |
| Standard | EN12530 - Devices Castors |
| Load capacity at 3 km/h | 80 kg |
| Load capacity Static | 160 kg |
| Temperature range (Minimum) | -20 °C |
| Temperature range (Maximum) | 85 °C |
| Overall height | 138 mm |
| Overall weight | 1.078 kg |

WHEEL

| | |
|-----------------------|---------------------------|
| Body material | Sheet Steel |
| Tread material | Solid rubber, non-marking |
| Bearing | Cone ball bearing |
| Threadguards | With threadguard |
| Diameter | 100 mm |
| Tread width | 32 mm |
| Hardness of tread (A) | 80 Shore A |

HOUSING

| | |
|---------------------|---------------------|
| Material fork | Steel sheet, medium |
| Fork shape | Broad |
| Swivel bearing | Two ball races |
| Offset | 38 mm |
| Swivel radius | 88 mm |
| Swivel interference | 176 mm |

FITTING

| | |
|---------------|-------------------------------------|
| Fitting type | Stem with cam hole for profile bars |
| Bolt diameter | 28 mm |
| Bolt length | 96 mm |