

# NOVATECH

FTX140x60-Ø12 HL65-A

EAN 4031582332070



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

|                      |             |
|----------------------|-------------|
| Roll Performance     | ● ● ● ● ○ ○ |
| Movement Noise       | ● ● ● ● ○ ○ |
| Attrition            | ● ● ● ● ● ○ |
| Corrosion Resistance | ● ● ● ● ○ ○ |

## CORE ATTRIBUTES

|                             |          |
|-----------------------------|----------|
| Product Name                | Novatech |
| Type                        | Wheel    |
| Load capacity at 3 km/h     | 700 kg   |
| Electric Conductive         | No       |
| Stainless                   | No       |
| Load capacity Static        | 1400 kg  |
| Temperature range (Minimum) | -20 °C   |
| Temperature range (Maximum) | 60 °C    |
| Overall weight              | 2.99 kg  |

## WHEEL

|                       |                                |
|-----------------------|--------------------------------|
| Body material         | Cast iron                      |
| Tread Material Mix    | Polyurethane, casted           |
| Bearing               | Precision ball bearing, sealed |
| Threadguards          | With threadguard               |
| Diameter              | 140 mm                         |
| Tread width           | 60 mm                          |
| Axle Hole Diameter    | 12 mm                          |
| Hub Length            | 65 mm                          |
| Hardness of tread (A) | 92 Shore A                     |
| Bearing type          | 6006 2RS                       |
| Sealing type          | A                              |
| Suitable for          | bt_linde                       |

