

## GALEA STAINLESS

5087PIO125P30-10

EAN 4031582370942



BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

## PERFORMANSE

Performanse kotrljanja ●●●○○

Buka u pokretu ●●●○○

Ishrana ●●●○○

otpornost na rdju ●●●●●

## OSNOVNI ATRIBUTI

Naziv proizvoda	Galea stainless
Tip	Okreni Tocak sa potpuna kocnica
Standard	EN12530 - Kastori uređaja
Nosivost na 3 km/h	80 kg
nerdjajuci	✓
Statički Nosivost	160 kg
Temperaturni opseg (Minimalno)	-20 °C
Opseg temperature (maksimalni)	60 °C
Sveukupna visina	162 mm
Ukupna težina	0,575 kg

## TOCAK

Materijal za telo	polipropilen
materijal omotaca	Cvrsta guma, bez obeležavanja
Nošenje	klizni lezaj
stitnici omotaca	Bez stražara
Prečnik	125 mm
Širina omotac	30 mm
Teškoća gazećeg omotac (A)	87 Šora A

## KUCISTE

Materijal	poliamid
oblik viljuska	Zatvoreno
okretni lezaj	Dve trke za loptu, Ojacano ili nerdjajuci
ofset	40 mm
Otpor okretanju	205 mm

## PRILAGOĐAVANJE

Tip uklapanja	otvor za vijak
dimenzija rupa sraf	10 mm

# GALEA STAINLESS

5087PIO125P30-10

EAN 4031582370942



BETTER MOBILITY. BETTER LIFE.

## TEHNIČKI CRTEŽI

