

# DURATECH

RK.TOP080X70-Ø47X14

EAN 4031582443103



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

Roll performance	● ● ● ● ●
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ●
Corrosion resistance	● ● ● ○ ○

## CORE ATTRIBUTES

Product name	Duratech
Housing type	Wheel
Load capacity at 1.8 mph	1433 lb
Load capacity Static	2866.01 lb
Temperature range (Minimum)	-40 °F
Temperature range (Maximum)	176 °F
Overall weight	0.55 lb

## WHEEL

Body material	Undefined
Tread material	Polypropylene, soft
Diameter	3.15 in
Tread width	2.76 in
Ball bearing diameter	1.85 in
Ball bearing width	0.55 in

# DURATECH

RK.TOP080X70-Ø47X14

EAN 4031582443103



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

