



BETTER MOBILITY. BETTER LIFE.

P10-40X17 / 8

EAN 4031582320114
Order number 00071744



Image may differ from the original product

PERFORMANCE

Corrosion resistance ● ● ● ○ ○

CORE ATTRIBUTES

Product name	Accessory
Housing type	Accessory
Load capacity at 1.8 mph	88.18 lb
Load capacity Static	176.37 lb
Overall height	0.31 in
Overall weight	0.09 lb

FITTING

Fitting type	Stem with U-shaped plate
Plate length	1.57 in
Plate width	0.67 in
Plate hole length (Maximum)	1.26 in
Plate hole width (Maximum)	1.26 in
Plate hole diameter	0.16 in