

# DURATECH

MOP 150X80-Ø35 HL90

EAN 4031582320039  
Order number 00830848



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## WHEEL

Body material	Polyamide, super heavy
Tread material	Identical with wheel body
Bearing	Precision ball bearing
Wheel color	Natural white
Threadguards	Without threadguard
Diameter	150 mm
Tread width	80 mm
Axle hole diameter	35 mm
Hub length	90 mm
Body width	80 mm
Hardness of tread (D)	75 Shore D
Bearing type	6207

## PERFORMANCE

Roll performance	● ● ● ● ●
Movement noise	● ● ○ ○ ○
Attrition	● ● ● ● ●
Corrosion resistance	● ● ● ○ ○

## CORE ATTRIBUTES

Product name	Duratech
Standard	EN12533 - Heavy Duty Castors
Load capacity at 4 km/h	3600 kg
Load capacity at 6 km/h	3000 kg
Load capacity Static	6000 kg
Temperature range (Minimum)	-40 °C
Temperature range (Maximum)	80 °C
Overall weight	2.025 kg

# DURATECH

MOP 150X80-Ø35 HL90

EAN 4031582320039  
Order number 00830848



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

