

NOVATECH

ETP 080X70-Ø20 HL70

EAN 4031582318623
Broj porudžbine 00801021

BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

TOCAK

Materijal za telo	Čelik, gvožđe
materijal omotaca	Poliuretana, liveno
Nošenje	precizini kuglicni lezaj
Boja Tocak	Med žuta (RAL1005)
stitnici omotaca	Sa threadguard
Prečnik	80 mm
Širina omotac	70 mm
dimenzija rupa osovina	20 mm
dužina glavcine	70 mm
Širina tela	70 mm
Teškoća gazećeg omotac (A)	92 Šor A
Teškoća gazećeg omotac (D)	42 Šor D
Tip ležaja	6204

PERFORMANSE

Performanse kotrljanja ●●●●○

Buka u pokretu ●●●○○

Ishrana ●●●●○

otpornost na rdju ●●●○○

OSNOVNI ATRIBUTI

Naziv proizvoda	Novatech
Tip	Tocak
Standard	EN12532 - transportna oprema
Nosivost na 4 km/h	700 kg
Nosivost na 6 km/h	560 kg
Statički Nosivost	1400 kg
Temperaturni opseg (Minimalno)	-10 °C
Opseg temperature (maksimalni)	60 °C
Ukupna težina	1,092 kg

NOVATECH

ETP 080X70-Ø20 HL70

EAN 4031582318623

Broj porudžbine 00801021



BETTER MOBILITY. BETTER LIFE.

TEHNIČKI CRTEŽI

