PRODUCT INFORMATION

ALPHA STAINLESS

8478UFD200P63

EAN 4031582347180



Image may differ from the original product

PERFORMANCE

Roll Performance	●●●●○
Movement Noise	●●●●○
Attrition	●●●○○
Corrosion Resistance	●●●●●

CORE ATTRIBUTES

Product Name	Alpha stainless
Type	Fixed castor
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	400 kg
Electric Conductive	No
Stainless	Yes
Load capacity Static	800 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	80 °C
Overall Height	240 mm
Overall width	115 mm
Overall weight	2.21 kg

HOUSING

Housing Material	Stainless steel, heavy
Fork shape	Broad
Housing Color	Stainless steel

WHEEL

Tread hardness	soft
Body material	Polyamide
Tread Material Mix	Elastic tire, non-marking, vulcanized
Bearing	Roller bearing, stainless
Axle	Screwed with nut
Wheel Color	Silver grey (RAL7001)
Diameter	200 mm
Tread width	46 mm
Body width	46 mm
Hardness of tread (A)	63 Shore A

FITTING

Fitting type	Medium rectangular plate
Plate length	140 mm
Plate width	115 mm
Plate hole length (Minimum)	75 mm
Plate hole length (Maximum)	80 mm
Plate hole width (Minimum)	75 mm
Plate hole width (Maximum)	105 mm
Plate hole diameter	11 mm

© Copyright 2026 TENTE International GmbH


ALPHA STAINLESS


8478UFD200P63

EAN 4031582347180

Order number 00035542

Product Drawings





© Copyright 2026 TENTE International GmbH