

# PURETECH

DIK 150x32-Ø8,1

EAN 4031582070170



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

|                      |           |
|----------------------|-----------|
| Roll Performance     | ● ● ● ○ ○ |
| Movement noise       | ● ● ● ● ○ |
| Attrition            | ● ● ● ○ ○ |
| Corrosion resistance | ● ● ● ○ ○ |

## CORE ATTRIBUTES

|                             |                           |
|-----------------------------|---------------------------|
| Product name                | Puretech                  |
| Type                        | Wheel                     |
| Standard                    | EN12530 - Devices Castors |
| Load capacity at 1.8 mph    | 220.46 lb                 |
| Electric conductive         | no                        |
| Stainless                   | no                        |
| Load capacity Static        | 440.92 lb                 |
| Temperature range (Minimum) | -4 °F                     |
| Temperature range (Maximum) | 185 °F                    |
| Overall weight              | 1.98 lb                   |

## WHEEL

|                       |                           |
|-----------------------|---------------------------|
| Body material         | Sheet Steel               |
| Tread material        | Solid rubber, non-marking |
| Bearing               | Cone ball bearing         |
| Wheel color           | Blue passivated           |
| Threadguards          | With threadguard          |
| Diameter              | 5.91 in                   |
| Tread width           | 1.26 in                   |
| Axle hole diameter    | 0.31 in                   |
| Hub length            | 1.42 in                   |
| Body width            | 1.26 in                   |
| Hardness of tread (A) | 80 Shore A                |

# PURETECH

DIK 150x32-Ø8,1

EAN 4031582070170

Order number 00000163  
Product Drawings



BETTER MOBILITY. BETTER LIFE.

