

ELASTECH

EEZ 200X75-Ø100 DG

EAN 4031582318333
Order number 00830872



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

Body material	Steel, iron
Tread material	Elastic tire, black, vulcanized
Bearing	Borehole, unmachined
Wheel color	Jet black (similar RAL9005)
Diameter	200 mm
Tread width	75 mm
Axle hole diameter	100 mm
Hub length	75 mm
Body width	75 mm
Hardness of tread (A)	68 Shore A

PERFORMANCE

Roll performance	● ● ● ● ●
Movement noise	● ● ● ● ●
Attrition	● ● ● ● ●
Corrosion resistance	● ● ● ● ●

CORE ATTRIBUTES

Product name	Elastech
Housing type	Wheel
Standard	EN12533 - Heavy Duty Castors
Load capacity at 4 km/h	600 kg
Load capacity at 6 km/h	500 kg
Load capacity Static	1000 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	85 °C
Overall weight	2.306 kg

ELASTECH

EEZ 200X75-Ø100 DG

EAN 4031582318333
Order number 00830872



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

