

# COMPACTA

1430UOI045P60-55x39

EAN 4031582010046



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

Roll Performance	● ● ● ● ○
Movement Noise	● ● ● ● ○
Attrition	● ● ● ● ●
Corrosion Resistance	● ● ● ● ○

## CORE ATTRIBUTES

Product Name	Compacta
Type	Swivel castor
Standard	EN12528 - Furniture Castors
Load capacity at 3 km/h	40 kg
Electric Conductive	No
Stainless	No
Load capacity Static	80 kg
Temperature range (Minimum)	-40 °C
Temperature range (Maximum)	80 °C
Overall Height	54 mm
Overall weight	0.09 kg

## HOUSING

Housing Material	Steel sheet, light
Fork shape	Broad
Swivel Bearing	One ball race
Housing Color	Blue passivated
Offset	22 mm
Swivel radius	44.5 mm
Swivel interference	89 mm

## WHEEL

Body material	Polyamide
Tread Material Mix	Identical with wheel body
Bearing	Plain bearing with spacer tube
Axle	Riveted
Threadguards	Without threadguard
Diameter	45 mm
Tread width	18 mm
Hardness of tread (D)	75 Shore D

## FITTING

Fitting type	Rectangular plate
Plate length	55 mm
Plate width	39 mm
Plate hole length (Maximum)	43 mm
Plate hole width (Maximum)	27 mm
Plate hole diameter	6.2 mm

# COMPACTA

1430UOI045P60-55x39

EAN 4031582010046



BETTER MOBILITY. BETTER LIFE.

## Product Drawings

