

SCOUT

814WUFC200P60 180° SMART

EAN 4031582429947



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

| | |
|----------------------|-----------|
| Roll performance | ● ● ● ○ ○ |
| Movement noise | ● ● ● ● ● |
| Attrition | ● ● ● ○ ○ |
| Corrosion resistance | ● ● ● ○ ○ |

CORE ATTRIBUTES

| | |
|-----------------------------|---|
| Product name | Scout |
| Type | Swivel castor with spring loaded directional lock and wheel brake |
| Load capacity at 3 km/h | 150 kg |
| Load capacity at 4 km/h | 150 kg |
| Stainless | ✓ |
| Temperature range (Minimum) | -20 °C |
| Temperature range (Maximum) | 80 °C |
| Overall height | 242 mm |
| Overall width | 72 mm |
| Overall weight | 3.143 kg |

WHEEL

| | |
|-----------------------|---------------------------------------|
| Body material | Polyamide |
| Tread hardness | soft |
| Tread material | Elastic tire, non-marking, vulcanized |
| Bearing | Precision ball bearing, stainless |
| Threadguards | With threadguard |
| Diameter | 200 mm |
| Tread width | 40 mm |
| Hardness of tread (A) | 64 Shore A |

HOUSING

| | |
|---------------------|------------------------|
| Material fork | Stainless steel, heavy |
| Fork shape | Angular |
| Swivel bearing | Precision ball bearing |
| Offset | 50 mm |
| Swivel radius | 162 mm |
| Swivel interference | 324 mm |

FITTING

| | |
|-----------------------------|-------------------|
| Fitting type | Rectangular plate |
| Plate length | 130 mm |
| Plate width | 74 mm |
| Plate hole length (Maximum) | 110 mm |
| Plate hole width (Maximum) | 50 mm |
| Plate hole diameter | 10.5 mm |

SCOUT

814WUFC200P60 180° SMART

EAN 4031582429947



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

