

ZETA

4687ICP160P63-75A

EAN 4031582478105



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ● ○
Movement noise	● ● ● ● ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Zeta
Type	Swivel castor with total lock
Standard	EN12533 - Heavy Duty Castors
Load capacity at 2.5 mph	1212.54 lb
Load capacity at 3.7 mph	970.03 lb
Load capacity Static	2425.08 lb
Temperature range (Minimum)	-4 °F
Temperature range (Maximum)	158 °F
Overall height	7.87 in
Overall weight	7.68 lb

WHEEL

Body material	Aluminum
	soft
Tread material	Ultratech Polyurethane, casted
Bearing	Precision ball bearing
Axle	Screwed with nut
Threadguards	Without threadguard
Diameter	6.3 in
Tread width	1.97 in
Hardness of tread (A)	75 Shore A

HOUSING

Material	Steel sheet, very heavy
Fork shape	Broad, reinforced
Swivel bearing	Two ball races, reinforced or stainless
Offset	2.17 in
Swivel radius	6.34 in
Swivel interference	12.68 in

FITTING

Fitting type	Rectangular plate
Plate length	5.39 in
Plate width	4.13 in
Plate hole length (Maximum)	4.13 in
Plate hole width (Minimum)	2.95 in
Plate hole width (Maximum)	3.15 in
Plate hole diameter	0.43 in

ZETA

4687ICP160P63-75A

EAN 4031582478105



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

