PRODUCT INFORMATION

INTEGRAL

2046UAP125R26-28S30 4xM8

EAN 4031582456844



Image may differ from the original product

PERFORMANCE

Roll Performance	●●●○○
Movement noise	●●●○○
Attrition	●●●●○
Corrosion resistance	●●●○○

CORE ATTRIBUTES

Product name	Integral
Type	Swivel caster with central , total lock
Standard	similar EN12531- Hospital Bed Castors
Load capacity at 1.8 mph	330.69 lb
Load capacity at 2.5 mph	330.69 lb
Electric conductive	no
Stainless	no
Load capacity Static	661.39 lb
Temperature range (Minimum)	-22 °F
Temperature range (Maximum)	176 °F
Overall height	6.22 in
Overall weight	2.15 lb
Certification	Tested and monitored by TÜV Süd

HOUSING

Housing Material	Steel sheet, medium
Fork shape	Closed
Swivel bearing	Precision ball bearing
Offset	1.38 in
Swivel radius	3.84 in
Swivel interference	7.68 in

WHEEL

Body material	Polyamide
Tread material	Polyurethane, injected
Bearing	Precision ball bearing
Threadguards	Integrated threadguard
Diameter	4.92 in
Tread width	1.26 in
Hardness of tread (D)	42 Shore D

FITTING

Fitting type	Stem with cam hole for profile bars
Bolt diameter	1.1 in
Bolt length	3.78 in

IF Design Award

Red Dot Design Award

© Copyright 2026 TENTE International GmbH


INTEGRAL

2046UAP125R26-28S30 4xM8

EAN 4031582456844

BETTER MOBILITY. BETTER LIFE.

Product Drawings



IF Design Award

Red Dot Design Award

© Copyright 2026 TENTE International GmbH