

KAPPA LOAD

9652FTP200P63 CL67

EAN 4031582314731



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll Performance	● ● ● ● ● ○
Movement noise	● ● ● ● ○ ○
Attrition	● ● ● ● ● ○
Corrosion resistance	● ● ● ● ● ○

CORE ATTRIBUTES

Product name	Kappa load
Type	Swivel caster with total lock, head end of caster
Standard	EN12533 - Heavy Duty Castors
Load capacity at 2.5 mph	2645.54 lb
Load capacity at 3.7 mph	2204.62 lb
Electric conductive	no
Stainless	no
Load capacity Static	4409.24 lb
Temperature range (Minimum)	14 °F
Temperature range (Maximum)	140 °F
Overall height	9.65 in
Overall width	4.57 in
Overall weight	17.07 lb

HOUSING

Housing Material	Cast iron, or iron forged, heavy
Fork shape	Broad, reinforced
Swivel bearing	Deep-groove ball thrust roller bearing
Housing Color	Blue passivated
Offset	2.32 in
Swivel radius	6.3 in
Swivel interference	12.6 in
Lubrication nipple	1
Dome diameter	4.37 in

WHEEL

Body material	Casting
Tread material	Polyurethane, casted
Bearing	Precision ball bearing
Axle	Screwed with nut
Wheel color	Honey yellow (RAL1005)
Threadguards	With threadguard
Diameter	7.87 in
Tread width	1.97 in
Body width	1.97 in
Hardness of tread (A)	92 Shore A
Hardness of tread (D)	42 Shore D

FITTING

Fitting type	Rectangular plate
Plate length	5.31 in
Plate width	4.33 in
Plate hole length (Minimum)	2.95 in
Plate hole length (Maximum)	3.15 in
Plate hole width (Minimum)	2.95 in
Plate hole width (Maximum)	4.13 in
Plate hole diameter	0.43 in

KAPPA LOAD

9652FTP200P63 CL67

EAN 4031582314731

Order number 00806570

Product Drawings



BETTER MOBILITY. BETTER LIFE.

