

PRODUCT INFORMATION

# BASETECH

POR 108x36-Ø12 HL44,4

EAN 4031582320794



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## WHEEL

Body material	Polypropylene
Tread material	Identical with wheel body
Bearing	Roller bearing
Wheel color	Graphite black (RAL9011)
Threadguards	Without threadguard
Diameter	4.25 in
Tread width	1.42 in
Axle hole diameter	0.47 in
Hub length	1.75 in
Body width	1.42 in
Hardness of tread (D)	65 Shore D

## PERFORMANCE

Roll Performance	● ● ● ● ○ ○
Movement noise	● ● ● ● ○ ○
Attrition	● ● ● ● ● ○
Corrosion resistance	● ● ● ● ○ ○

## CORE ATTRIBUTES

Product name	Basetech
Type	Wheel
Standard	EN12532 - Transport Equipment
Load capacity at 2.5 mph	352.74 lb
Electric conductive	no
Stainless	no
Load capacity Static	705.48 lb
Temperature range (Minimum)	-4 °F
Temperature range (Maximum)	140 °F
Overall weight	0.34 lb

# BASETECH

POR 108x36-Ø12 HL44,4

EAN 4031582320794

Order number 00030953  
Product Drawings



BETTER MOBILITY. BETTER LIFE.

