

DURATECH HEAT

BOG100X35-Ø8 HL45,5 (CASQUILLO ZINC)

EAN 4031582456486



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ●
Corrosion resistance	● ● ● ● ●

CORE ATTRIBUTES

Product name	Duratech heat
Type	Wheel
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	125 kg
Load capacity Static	250 kg
Temperature range (Minimum)	-40 °C
Temperature range (Maximum)	280 °C
Overall weight	0.252 kg

WHEEL

Body material	Plastic thermoset, heat-resistant
Tread material	Identical with wheel body
Bearing	Dry bearing bush
Diameter	100 mm
Tread width	35 mm
Axle hole diameter	8 mm
Hub length	45 mm
Hardness of tread (D)	85 Shore D

DURATECH HEAT

BOG100X35-Ø8 HL45,5 (CASQUILLO ZINC)

EAN 4031582456486



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

