

NOVATECH

FTF250X75-Ø80-4XØ15

EAN 4031582331707



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Novatech
Housing type	Wheel
Temperature range (Minimum)	-4 °F
Temperature range (Maximum)	140 °F
Overall weight	19.12 lb

WHEEL

Body material	Casting
Tread material	Polyurethane, casted
Bearing	Flanged wheel
Diameter	9.84 in
Tread width	2.95 in
Axle hole diameter	3.15 in
Hardness of tread (A)	92 Shore A
Hole circle diameter	4.41 in
Fitting hole diameter	0.59 in
Suitable for	atlet

FITTING

Bolt mounting holes quantity	4
------------------------------	---

TECHNICAL DRAWINGS

