

PRODUCT INFORMATION

DURATECH

U00125x43-Ø12 HL 58

EAN 4031582419023



Image may differ from the original product

PERFORMANCE

Roll Performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ●
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Duratech
Type	Wheel
Standard	EN12532 - Transport Equipment
Load capacity at 2.5 mph	661.39 lb
Electric conductive	no
Stainless	no
Load capacity Static	1322.77 lb
Temperature range (Minimum)	-40 °F
Temperature range (Maximum)	176 °F
Overall weight	0.54 lb



BETTER MOBILITY. BETTER LIFE.

WHEEL

Body material	Polyamide
Tread material	Identical with wheel body
Bearing	Plain bearing
Threadguards	Without threadguard
Diameter	4.92 in
Tread width	1.69 in
Axle hole diameter	0.79 in
Hub length	2.28 in
Hardness of tread (D)	75 Shore D

DURATECH

U00125x43-Ø12 HL 58

EAN 4031582419023



BETTER MOBILITY. BETTER LIFE.

Product Drawings

U00125x43-Ø12 NL58

