

PRODUCT INFORMATION

PURETECH AIR

DQP400x100-Ø20 HL74 4PR

EAN 4031582318029



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

|                      |           |
|----------------------|-----------|
| Roll Performance     | ● ● ● ○ ○ |
| Movement noise       | ● ● ● ○ ○ |
| Attrition            | ● ● ● ○ ○ |
| Corrosion resistance | ● ● ● ○ ○ |

CORE ATTRIBUTES

|                          |              |
|--------------------------|--------------|
| Product name             | Puretech air |
| Type                     | Wheel        |
| Load capacity at 1.8 mph | 440.92 lb    |
| Electric conductive      | no           |
| Stainless                | no           |
| Load capacity Static     | 881.85 lb    |
| Overall weight           | 5.88 lb      |

WHEEL

|                       |                               |
|-----------------------|-------------------------------|
| Tread hardness        | soft                          |
| Body material         | Sheet Steel                   |
| Tread material        | Pneumatic tire, block profile |
| Bearing               | Precision ball bearing        |
| Threadguards          | With threadguard              |
| Diameter              | 15.75 in                      |
| Tread width           | 3.94 in                       |
| Axle hole diameter    | 0.79 in                       |
| Hub length            | 2.91 in                       |
| Hardness of tread (A) | 55 Shore A                    |

# PURETECH AIR

DQP400x100-Ø20 HL74 4PR

EAN 4031582318029



BETTER MOBILITY. BETTER LIFE.

## Product Drawings

