PRODUCT INFORMATION

PURETECH AIR

DQP400x100-Ø20 HL74 4PR

EAN 4031582318029



Image may differ from the original product

PERFORMANCE

Roll Performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Puretech air
Type	Wheel
Load capacity at 1.8 mph	440.92 lb
Electric conductive	no
Stainless	no
Load capacity Static	881.85 lb
Overall weight	5.88 lb

WHEEL

Tread hardness	soft
Body material	Sheet Steel
Tread material	Pneumatic tire, block profile
Bearing	Precision ball bearing
Threadguards	With threadguard
Diameter	15.75 in
Tread width	3.94 in
Axle hole diameter	0.79 in
Hub length	2.91 in
Hardness of tread (A)	55 Shore A

© Copyright 2026 TENTE International GmbH


PURETECH AIR

DQP400x100-Ø20 HL74 4PR

EAN 4031582318029

BETTER MOBILITY. BETTER LIFE.

Product Drawings



© Copyright 2026 TENTE International GmbH