PRODUCT INFORMATION

ALPHA

3478UOO125P62

EAN 4031582030129



Image may differ from the original product

PERFORMANCE

Roll Performance	●●●○○
Movement Noise	●●●○○
Attrition	●●●●○
Corrosion Resistance	●●●○○

CORE ATTRIBUTES

Product Name	Alpha
Type	Fixed castor
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	250 kg
Electric Conductive	No
Stainless	No
Load capacity Static	500 kg
Temperature range (Minimum)	-40 °C
Temperature range (Maximum)	80 °C
Overall Height	155 mm
Overall width	85 mm
Overall weight	0.61 kg

HOUSING

Housing Material	Steel sheet, heavy
Fork shape	Broad
Housing Color	Blue passivated

WHEEL

Body material	Polyamide
Tread Material Mix	Identical with wheel body
Bearing	Plain bearing
Axle	Screwed with nut
Wheel Color	Natural white
Threadguards	Without threadguard
Diameter	125 mm
Tread width	40 mm
Body width	40 mm
Hardness of tread (D)	75 Shore D

FITTING

Fitting type	Small rectangular plate
Plate length	103 mm
Plate width	85 mm
Plate hole length (Minimum)	77 mm
Plate hole length (Maximum)	60 mm
Plate hole width (Minimum)	77 mm
Plate hole width (Maximum)	80 mm
Plate hole diameter	9 mm

© Copyright 2026 TENTE International GmbH


ALPHA


3478UOO125P62

EAN 4031582030129

Order number 00004949

Product Drawings





© Copyright 2026 TENTE International GmbH