

NOVATECH

ETP 080X54-Ø20 HL54

EAN 4031582318562
Broj porudžbine 00830660

BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

PERFORMANSE

Performanse kotrljanja ●●●●○

Buka u pokretu ●●●○○

Ishrana ●●●●○

otpornost na rdju ●●●○○

OSNOVNI ATRIBUTI

| | |
|--------------------------------|------------------------------|
| Naziv proizvoda | Novatech |
| Tip | Tocak |
| Standard | EN12532 - transportna oprema |
| Nosivost na 4 km/h | 500 kg |
| Nosivost na 6 km/h | 400 kg |
| Statički Nosivost | 1000 kg |
| Temperaturni opseg (Minimalno) | -10 °C |
| Opseg temperature (maksimalni) | 60 °C |
| Ukupna težina | 0,87 kg |

TOCAK

| | |
|----------------------------|--------------------------|
| Materijal za telo | Čelik, gvožđe |
| materijal omotaca | Poliuretana, liveno |
| Nošenje | precizini kuglicni lezaj |
| Boja Tocak | Med žuta (RAL1005) |
| stitnici omotaca | Sa threadguard |
| Prečnik | 80 mm |
| Širina omotac | 54 mm |
| dimenzija rupa osovina | 20 mm |
| dužina glavčine | 54 mm |
| Širina tela | 54 mm |
| Teškoća gazećeg omotac (A) | 92 Šor A |
| Teškoća gazećeg omotac (D) | 42 Šor D |
| Tip ležaja | 6204 |

NOVATECH

ETP 080X54-Ø20 HL54

EAN 4031582318562
Broj porudžbine 00830660



BETTER MOBILITY. BETTER LIFE.

TEHNIČKI CRTEŽI

