

# AGILA

2477PJO075B10-11X31

EAN 4031582403770  
Order number 00004458



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

|                      |           |
|----------------------|-----------|
| Roll performance     | ● ● ● ○ ○ |
| Movement noise       | ● ● ● ● ○ |
| Attrition            | ● ● ● ○ ○ |
| Corrosion resistance | ● ● ● ○ ○ |

## CORE ATTRIBUTES

|                             |                               |
|-----------------------------|-------------------------------|
| Product name                | Agila                         |
| Housing type                | Swivel castor with total lock |
| Standard                    | EN12530 - Devices Castors     |
| Load capacity at 3 km/h     | 75 kg                         |
| Load capacity Static        | 150 kg                        |
| Temperature range (Minimum) | -20 °C                        |
| Temperature range (Maximum) | 60 °C                         |
| Overall height              | 103 mm                        |
| Overall width               | 43 mm                         |
| Overall weight              | 0.299 kg                      |

## WHEEL

|                       |                       |
|-----------------------|-----------------------|
| Body material         | Polypropylene         |
| Tread material        | Thermoplastic rubber  |
| Bearing               | Plain bearing         |
| Wheel color           | Silver grey (RAL7001) |
| Threadguards          | Without threadguard   |
| Diameter              | 75 mm                 |
| Tread width           | 25 mm                 |
| Body width            | 25 mm                 |
| Hardness of tread (A) | 87 Shore A            |

## HOUSING

|                     |                     |
|---------------------|---------------------|
| Material fork       | Steel sheet, medium |
| Fork shape          | Broad               |
| Swivel bearing      | Two ball races      |
| Colour              | Blue passivated     |
| Offset              | 24 mm               |
| Swivel radius       | 80 mm               |
| Swivel interference | 160 mm              |
| Dome diameter       | 43 mm               |

## FITTING

|               |                                  |
|---------------|----------------------------------|
| Fitting type  | Stem with grip ring, with collar |
| Stem diameter | 11 mm                            |
| Stem length   | 31 mm                            |

## PRODUCT INFORMATION

# AGILA

2477PJO075B10-11X31

EAN 4031582403770  
Order number 00004458



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

---

