

COMPACTA

1430PJI025P60-35X30 CONVEX

EAN 4031582474183



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Compacta
Type	Swivel castor
Standard	EN12528 - Furniture Castors
Load capacity at 3 km/h	10 kg
Load capacity Static	20 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall height	35 mm
Overall weight	0.071 kg

WHEEL

Body material	Polypropylene
Tread hardness	soft
Tread profile	convex
Tread material	Thermoplastic rubber
Bearing	Plain bearing with spacer tube
Axle	Riveted
Threadguards	Without threadguard
Diameter	25 mm
Tread width	12 mm
Hardness of tread (A)	75 Shore A

HOUSING

Material fork	Steel sheet, light
Fork shape	Broad
Swivel bearing	One ball race
Offset	7.5 mm
Swivel radius	22.5 mm
Swivel interference	45 mm

FITTING

Fitting type	Rectangular plate
Plate length	35 mm
Plate width	30 mm
Plate hole length (Maximum)	23 mm
Plate hole width (Maximum)	28 mm
Plate hole diameter	4.2 mm

PRODUCT INFORMATION

COMPACTA

1430PJI025P60-35X30 CONVEX

EAN 4031582474183



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

