

MAXTECH

UAD200X50-Ø20 HL58 BURDEOS

EAN 4031582416411



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

| | |
|-----------------------|---------------------------|
| Body material | Polyamide |
| Tread material | Polyurethane, injected |
| Bearing | Roller bearing, stainless |
| Diameter | 200 mm |
| Tread width | 50 mm |
| Axle hole diameter | 20 mm |
| Hub length | 58 mm |
| Hardness of tread (D) | 42 Shore D |

PERFORMANCE

| | |
|----------------------|-----------|
| Roll performance | ● ● ● ○ ○ |
| Movement noise | ● ● ● ○ ○ |
| Attrition | ● ● ● ● ○ |
| Corrosion resistance | ● ● ● ○ ○ |

CORE ATTRIBUTES

| | |
|-----------------------------|-------------------------------|
| Product name | Maxtech |
| Type | Wheel |
| Standard | EN12532 - Transport Equipment |
| Load capacity at 4 km/h | 500 kg |
| Load capacity Static | 1000 kg |
| Temperature range (Minimum) | -40 °C |
| Temperature range (Maximum) | 80 °C |
| Overall weight | 0.91 kg |

MAXTECH

UAD200X50-Ø20 HL58 BURDEOS

EAN 4031582416411



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

