

MAXTECH

UAR160X40-Ø20 HL58 BURDEOS

EAN 4031582442540



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Maxtech
Housing type	Wheel
Standard	EN12532 - Transport Equipment
Load capacity at 2.5 mph	771.62 lb
Load capacity Static	1543.23 lb
Temperature range (Minimum)	-13 °F
Temperature range (Maximum)	176 °F
Overall weight	1.39 lb

WHEEL

Body material	Polyamide
Tread material	Polyurethane, injected
Bearing	Roller bearing
Threadguards	Without threadguard
Diameter	6.3 in
Tread width	1.57 in
Axle hole diameter	0.79 in
Hub length	2.28 in
Hardness of tread (D)	40 Shore D

MAXTECH

UAR160X40-Ø20 HL58 BURDEOS

EAN 4031582442540



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

