

ELASTECH

UER 100X34-Ø12

EAN 4031582323290
Order number 00030961



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

| | |
|-----------------------|---------------------------------|
| Body material | Polyamide |
| Tread material | Elastic tire, black, vulcanized |
| Bearing | Roller bearing |
| Wheel color | Silver grey (RAL7001) |
| Threadguards | Without threadguard |
| Diameter | 100 mm |
| Tread width | 34 mm |
| Axle hole diameter | 12 mm |
| Hub length | 44.4 mm |
| Body width | 34 mm |
| Hardness of tread (A) | 63 Shore A |

PERFORMANCE

| | |
|----------------------|-----------|
| Roll performance | ● ● ● ● ○ |
| Movement noise | ● ● ● ● ○ |
| Attrition | ● ● ● ○ ○ |
| Corrosion resistance | ● ● ● ○ ○ |

CORE ATTRIBUTES

| | |
|-----------------------------|-------------------------------|
| Product name | Elastech |
| Standard | EN12532 - Transport Equipment |
| Load capacity at 4 km/h | 160 kg |
| Load capacity Static | 320 kg |
| Temperature range (Minimum) | -20 °C |
| Temperature range (Maximum) | 80 °C |
| Overall weight | 0.245 kg |

ELASTECH

UER 100X34-Ø12

EAN 4031582323290
Order number 00030961



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

