

# AGILA

2478DIK050P41-55

EAN 4031582030037  
Order number 00003897



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ● ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

## CORE ATTRIBUTES

Product name	Agila
Housing type	Fixed castor
Standard	EN12530 - Devices Castors
Load capacity at 1.8 mph	88.18 lb
Load capacity Static	176.37 lb
Temperature range (Minimum)	-4 °F
Temperature range (Maximum)	185 °F
Overall height	2.72 in
Overall width	1.38 in
Overall weight	0.35 lb

## WHEEL

Body material	Sheet Steel
Tread material	Solid rubber, non-marking
Bearing	Cone ball bearing
Wheel color	Blue passivated
Threadguards	With threadguard
Diameter	1.97 in
Tread width	0.75 in
Body width	0.75 in
Hardness of tread (A)	80 Shore A

## HOUSING

Material	Steel sheet, medium
Fork shape	Broad
Color	Blue passivated
Dome diameter	1.06 in

## FITTING

Fitting type	Square plate
Plate length	2.17 in
Plate width	2.17 in
Plate hole length (Minimum)	1.52 in
Plate hole length (Maximum)	1.73 in
Plate hole width (Minimum)	1.52 in
Plate hole width (Maximum)	1.73 in
Plate hole diameter	0.25 in

# AGILA

2478DIK050P41-55

EAN 4031582030037  
Order number 00003897



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

