PRODUCT INFORMATION

# STYLEA

5925UAI055L51-8

EAN 4031582406399

BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

| | |
|---|---|
| Roll Performance | ●●●○○ |
| Movement noise | ●●●○○ |
| Attrition | ●●●○○ |
| Corrosion resistance | ●●●●○ |

## CORE ATTRIBUTES

| | |
|---|---|
| Product name | Stylea |
| Type | Swivel caster with wheel brake |
| Standard | EN12528 - Furniture Castors |
| Load capacity at 1.8 mph | 88.18 lb |
| Electric conductive | no |
| Stainless | no |
| Load capacity Static | 176.37 lb |
| Temperature range (Minimum) | 14 °F |
| Temperature range (Maximum) | 104 °F |
| Overall height | 2.24 in |
| Overall width | 1.46 in |
| Overall weight | 1.59 lb |

## HOUSING

| | |
|---|---|
| Housing Material | Polyamide |
| Fork shape | Twin wheel housing |
| Swivel bearing | Stem, swiveling |
| Swivel radius | 1.85 in |
| Swivel interference | 3.7 in |
| Dome diameter | 0.71 in |

## WHEEL

| | |
|---|---|
| Body material | Polyamide |
| Tread material | Polyurethane, injected |
| Bearing | Plain bearing with spacer tube |
| Axle | Riveted |
| Threadguards | Without threadguard |
| Diameter | 2.17 in |
| Tread width | 0.43 in |
| Hardness of tread (A) | 92 Shore A |

## FITTING

| | |
|---|---|
| Fitting type | Blind hole for B10 fitting |
| Bolt hole diameter | 0.31 in |

© Copyright 2026 TENTE International GmbH


# STYLEA


5925UAI055L51-8

EAN 4031582406399

BETTER MOBILITY. BETTER LIFE.

## Product Drawings



© Copyright 2026 TENTE International GmbH