

NOVATECH

FTP250X50-Ø25 HL62

EAN 4031582331035



BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

TOCAK

Materijal za telo	Ливено Гвожђе
materijal omotaca	Poliuretana, liveno
Nošenje	precizini kuglicni lezaj
stitnici omotaca	Sa threadguard
Prečnik	250 mm
Širina omotac	50 mm
dimenzija rupa osovina	25 mm
duzina glavčine	62 mm
Teškoća gazećeg omotac (A)	92 Šor A

PERFORMANSE

Performanse kotrljanja	● ● ● ● ○
Buka u pokretu	● ● ● ○ ○
Ishrana	● ● ● ● ○
otpornost na rdju	● ● ● ○ ○

OSNOVNI ATRIBUTI

Naziv proizvoda	Novatech
Tip	Tocak
Standard	EN12533 - Tockoviza teske terete
Nosivost na 4 km/h	1440 kg
Nosivost na 6 km/h	1200 kg
Statički Nosivost	2880 kg
Temperaturni opseg (Minimalno)	-20 °C
Opseg temperature (maksimalni)	60 °C

NOVATECH

FTP250X50-Ø25 HL62

EAN 4031582331035



BETTER MOBILITY. BETTER LIFE.

TEHNIČKI CRTEŽI

