

AGILA

2470DYK075R07-Ø27-30

EAN 4031582340853



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

| | |
|----------------------|-----------|
| Roll Performance | ● ● ● ● ○ |
| Movement noise | ● ● ● ● ○ |
| Attrition | ● ● ● ● ○ |
| Corrosion resistance | ● ● ● ● ○ |

CORE ATTRIBUTES

| | |
|-----------------------------|---------------------------|
| Product name | Agila |
| Type | Swivel caster |
| Standard | EN12530 - Devices Castors |
| Load capacity at 1.8 mph | 121.25 lb |
| Electric conductive | Yes |
| Stainless | no |
| Load capacity Static | 242.51 lb |
| Temperature range (Minimum) | 14 °F |
| Temperature range (Maximum) | 104 °F |
| Overall height | 4.06 in |

HOUSING

| | |
|---------------------|---------------------|
| Housing Material | Steel sheet, medium |
| Fork shape | Broad |
| Swivel bearing | Two ball races |
| Housing Color | Blue passivated |
| Offset | 0.94 in |
| Swivel radius | 2.42 in |
| Swivel interference | 4.84 in |

WHEEL

| | |
|-----------------------|------------------------------------------|
| Body material | Sheet Steel |
| Tread material | Solid rubber, black, electric-conductive |
| Bearing | Cone ball bearing |
| Threadguards | With threadguard |
| Diameter | 2.95 in |
| Tread width | 0.98 in |
| Hardness of tread (A) | 80 Shore A |

FITTING

| | |
|----------------------------|------------------------------------------------------------|
| Fitting type | Synthetic expander, round |
| Expander fitting (Minimum) | 1.06 in |
| Expander fitting (Maximum) | 1.18 in |
| Hint | Please indicate required tube innerdiameter when ordering. |

AGILA

2470DYK075R07-Ø27-30

EAN 4031582340853



BETTER MOBILITY. BETTER LIFE.

Product Drawings

