

ELASTECH

UEP 200x46-Ø20

EAN 4031582328608



BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

TOČAK

Tread hardness	mekan
Materijal za telo	poliamid
materijal omotaca	Elastična guma, crna, vulkanizovana
Nošenje	precizini kuglični lezaj
Boja Tocak	Srebrna siva (RAL7001)
stitnici omotaca	Sa threadguard
Prečnik	200 mm
Širina omotac	46 mm
dimenzija rupa osovina	20 mm
dužina glavčine	60 mm
Širina tela	46 mm
Teškoća gazećeg omotac (A)	63 Šora A

PERFORMANSE

Performanse kotrljanja	● ● ● ● ○
Buka u pokretu	● ● ● ● ●
Ishrana	● ● ● ○ ○
otpornost na rdju	● ● ● ○ ○

OSNOVNI ATRIBUTI

Naziv proizvoda	Elastech
Tip	Tocak
Standard	EN12532 - transportna oprema
Nosivost na 4 km/h	400 kg
Električni provod	no
nerdjajući	no
Statički Nosivost	800 kg
Temperaturni opseg (Minimalno)	-20 °C
Opseg temperature (maksimalni)	80 °C
Ukupna težina	1.24 kg

ELASTECH

UEP 200x46-Ø20

EAN 4031582328608

Broj porudžbine 00023479
Product Drawings



BETTER MOBILITY. BETTER LIFE.

