

DURATECH

TOP 100X50-Ø20 HL60

EAN 4031582322675

Broj porudžbine 00801132



BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

TOCAK

Materijal za telo	poliamid težak
materijal omotaca	Identično sa telom Tocak
Nošenje	precizini kuglicni lezaj
Boja Tocak	Prirodno belo
stitnici omotaca	Bez stražara
Prečnik	100 mm
Širina omotac	50 mm
dimenzija rupa osovina	20 mm
dužina glavcine	60 mm
Širina tela	50 mm
Teškoća gazećeg omotac (D)	75 Šor D
Tip ležaja	6004

PERFORMANSE

Performanse kotrljanja	● ● ● ● ●
Buka u pokretu	● ● ○ ○ ○
Ishrana	● ● ● ● ●
otpornost na rdju	● ● ● ○ ○

OSNOVNI ATRIBUTI

Naziv proizvoda	Duratech
Standard	EN12533 - Tockovi za teske terete
Nosivost na 4 km/h	720 kg
Nosivost na 6 km/h	600 kg
Statički Nosivost	1200 kg
Temperaturni opseg (Minimalno)	-40 °C
Opseg temperature (maksimalni)	80 °C
Ukupna težina	0,527 kg

DURATECH

TOP 100X50-Ø20 HL60

EAN 4031582322675

Broj porudžbine 00801132



BETTER MOBILITY. BETTER LIFE.

TEHNIČKI CRTEŽI

