

ANIKA

5920UAI065L51-8 DOM18

EAN 4031582433401



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ● ○

CORE ATTRIBUTES

Product name	Anika
Type	Swivel castor
Standard	EN12528 - Furniture Castors
Load capacity at 1.8 mph	110.23 lb
Load capacity Static	220.46 lb
Temperature range (Minimum)	14 °F
Temperature range (Maximum)	104 °F
Overall height	2.64 in
Overall width	1.56 in
Overall weight	0.17 lb

WHEEL

Body material	Polyamide
Tread material	Polyurethane, injected
Bearing	Plain bearing with spacer tube
Axle	Riveted
Threadguards	Without threadguard
Diameter	2.56 in
Tread width	0.43 in
Hardness of tread (A)	92 Shore A

HOUSING

Material	Polyamide
Fork shape	Twin wheel housing
Swivel bearing	Stem, swiveling
Swivel radius	2.19 in
Swivel interference	4.37 in
Dome diameter	0.71 in

FITTING

Fitting type	Blind hole for B10 fitting
Bolt hole diameter	0.31 in



PRODUCT INFORMATION

ANIKA

5920UAI065L51-8 DOM18

EAN 4031582433401



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS



Interzum
Award