

SUPRATECH

PJI050X19-Ø8 NEGRA

EAN 4031582457285



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

Body material	Polypropylene
Tread material	Thermoplastic rubber
Bearing	Plain bearing with spacer tube
Threadguards	Without threadguard
Diameter	50 mm
Tread width	19 mm
Axle hole diameter	6 mm
Hub length	21.5 mm
Hardness of tread (A)	87 Shore A

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Supratech
Type	Wheel
Standard	EN12530 - Devices Castors
Load capacity at 3 km/h	40 kg
Load capacity Static	80 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall weight	0.021 kg

SUPRATECH

PJI050X19-Ø8 NEGRA

EAN 4031582457285



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

