

FOOTMASTER

FOOT MASTER GAPC-075-ASF-HUD

EAN 4031582496604
Order number 00800206



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	○ ○ ○ ○ ○
Movement noise	○ ○ ○ ○ ○
Attrition	○ ○ ○ ○ ○
Corrosion resistance	○ ○ ○ ○ ○

CORE ATTRIBUTES

Product name	Footmaster
Type	Swivel castor
Load capacity at 1.8 mph	220.46 lb
Temperature range (Minimum)	14 °F
Temperature range (Maximum)	194 °F
Overall height	3.98 in
Overall width	2.4 in
Overall weight	3.41 lb

WHEEL

Bearing	Unmachined hub
Diameter	2.95 in
Tread width	1.18 in
Body width	1.18 in

HOUSING

Offset	1.18 in
Swivel radius	2.68 in
Swivel interference	5.35 in
Dome diameter	2.28 in

FITTING

Plate length	3.74 in
Plate width	2.52 in
Plate hole length (Minimum)	3.07 in
Plate hole length (Maximum)	1.77 in
Plate hole width (Minimum)	3.07 in
Plate hole width (Maximum)	2.83 in
Plate hole diameter	0.35 in

FOOTMASTER

FOOT MASTER GAPC-075-ASF-HUD

EAN 4031582496604
Order number 00800206



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

