

PRODUCT INFORMATION

# GLIDE

A229POI050B10-11x20

EAN 4031582319606



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

### PERFORMANCE

Roll Performance	● ● ● ○ ○
Movement Noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion Resistance	● ● ● ○ ○

### CORE ATTRIBUTES

Product Name	Glide
Type	Customized solution
Load capacity at 3 km/h	30 kg
Electric Conductive	No
Stainless	No
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall Height	33 mm
Overall width	50 mm
Overall weight	0.06 kg

### HOUSING

Housing Material	Polypropylene
Fork shape	Straight
Swivel Bearing	Stem, swiveling
Dome diameter	38 mm
Collar diameter	50 mm

### WHEEL

Body material	Polypropylene
Tread Material Mix	Identical with wheel body
Bearing	Plain bearing with spacer tube
Threadguards	Without threadguard
Diameter	50 mm
Hardness of tread (D)	65 Shore D

### FITTING

Fitting type	Stem with grip ring, with collar
Stem diameter	11 mm

# GLIDE

A229POI050B10-11x20

EAN 4031582319606

Order number 00072176

**Product Drawings**



BETTER MOBILITY. BETTER LIFE.

