

PRODUCT INFORMATION

GLIDE

A229POI050B10-11x20

EAN 4031582319606



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll Performance	● ● ● ● ○
Movement Noise	● ● ● ● ○
Attrition	● ● ● ● ○
Corrosion Resistance	● ● ● ● ○

CORE ATTRIBUTES

Product Name	Glide
Type	Customized solution
Load capacity at 3 km/h	30 kg
Electric Conductive	No
Stainless	No
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall Height	33 mm
Overall width	50 mm
Overall weight	0.06 kg

HOUSING

Housing Material	Polypropylene
Fork shape	Straight
Swivel Bearing	Stem, swiveling
Dome diameter	38 mm
Collar diameter	50 mm

WHEEL

Body material	Polypropylene
Tread Material Mix	Identical with wheel body
Bearing	Plain bearing with spacer tube
Threadguards	Without threadguard
Diameter	50 mm
Hardness of tread (D)	65 Shore D

FITTING

Fitting type	Stem with grip ring, with collar
Stem diameter	11 mm

GLIDE

A229POI050B10-11x20

EAN 4031582319606

Order number 00072176
Product Drawings



BETTER MOBILITY. BETTER LIFE.

