

PRODUCT INFORMATION

ELASTECH

IFP 300x55-Ø25 HL60

EAN 4031582366303



Image may differ from the original product

PERFORMANCE

Roll Performance	● ● ● ● ●
Movement Noise	● ● ● ● ●
Attrition	● ● ● ● ●
Corrosion Resistance	● ● ● ● ●

CORE ATTRIBUTES

Product Name	Elastech
Type	Wheel
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	600 kg
Load capacity at 6 km/h	480 kg
Electric Conductive	No
Stainless	No
Load capacity Static	1200 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	85 °C
Overall weight	3.58 kg



BETTER MOBILITY. BETTER LIFE.

WHEEL

Tread hardness	soft
Body material	Aluminium
Tread Material Mix	Elastic tire, non-marking, vulcanized
Bearing	Precision ball bearing
Wheel Color	Grey / non marking
Threadguards	Without threadguard
Diameter	300 mm
Tread width	55 mm
Axle Hole Diameter	25 mm
Hub Length	60 mm
Body width	55 mm
Hardness of tread (A)	68 Shore A

ELASTECH

IFP 300x55-Ø25 HL60


EAN 4031582366303

Order number 00837669

Product Drawings



BETTER MOBILITY. BETTER LIFE.




PRODUCT INFORMATION

ELASTECH

IFP 300x55-Ø25 H1.60

EAN 4031582366803

Order number 00317639



BETTER MOBILITY. BETTER LIFE.