

# NOVATECH

FTP 150X60-Ø25 HL60

EAN 4031582329520

Broj porudžbine 00827815



BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

## TOCAK

Materijal za telo	Ливено Гвожђе
materijal omotaca	Poliuretana, liveno
Nošenje	precizini kuglicni lezaj
Boja Tocak	Med žuta (RAL1005)
stitnici omotaca	Sa threadguard
Prečnik	150 mm
Širina omotac	60 mm
dimenzija rupa osovina	25 mm
dužina glavcine	60 mm
Širina tela	60 mm
Teškoća gazećeg omotac (A)	92 Šor A
Teškoća gazećeg omotac (D)	42 Šor D

## PERFORMANSE

Performanse kotrljanja ●●●●○

Buka u pokretu ●●●○○

Ishrana ●●●●○

otpornost na rdju ●●●○○

## OSNOVNI ATRIBUTI

Naziv proizvoda	Novatech
Tip	Tocak
Standard	EN12533 - Tockoviza teske terete
Nosivost na 4 km/h	960 kg
Nosivost na 6 km/h	800 kg
Statički Nosivost	1600 kg
Temperaturni opseg (Minimalno)	-10 °C
Opseg temperature (maksimalni)	60 °C
Ukupna težina	3,94 kg

# NOVATECH

FTP 150X60-Ø25 HL60

EAN 4031582329520

Broj porudžbine 00827815



BETTER MOBILITY. BETTER LIFE.

## TEHNIČKI CRTEŽI

