

KAPPA LOAD

9650MOP300P64 TFR

EAN 4031582481877



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll Performance	● ● ● ● ●
Movement Noise	● ● ● ○ ○
Attrition	● ● ● ● ●
Corrosion Resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product Name	Kappa load
Type	Swivel castor
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	2000 kg
Load capacity at 6 km/h	2000 kg
Electric Conductive	No
Stainless	No
Load capacity Static	4000 kg
Temperature range (Minimum)	-40 °C
Temperature range (Maximum)	80 °C
Overall Height	355 mm
Overall weight	15.74 kg

HOUSING

Housing Material	Iron forged, heavy
Fork shape	Broad, reinforced
Swivel Bearing	Deep-groove ball thrust roller bearing
Offset	76 mm
Swivel radius	226 mm
Swivel interference	452 mm
Lubrication nipple	1

WHEEL

Body material	Polyamide, super heavy
Tread Material Mix	Identical with wheel body
Bearing	Precision ball bearing
Axle	Screwed with nut
Threadguards	Without threadguard
Diameter	300 mm
Tread width	80 mm
Hardness of tread (D)	75 Shore D

FITTING

Fitting type	Large rectangular plate
Plate length	175 mm
Plate width	140 mm
Plate hole length (Maximum)	140 mm
Plate hole width (Maximum)	105 mm
Plate hole diameter	15 mm

KAPPA LOAD

9650MOP300P64 TFR

EAN 4031582481877



BETTER MOBILITY. BETTER LIFE.

Product Drawings

