

## GALEA STAINLESS

5085PJC125R05-22X40

EAN 4031582336527



BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

## PERFORMANSE

Performanse kotrljanja ●●●○○

Buka u pokretu ●●●○○

Ishrana ●●●○○

otpornost na rdju ●●●●●

## OSNOVNI ATRIBUTI

Naziv proizvoda	Galea stainless
Tip	Okreni Tocak sa kocnica tocka
Standard	EN12530 - Kastori uređaja
Nosivost na 3 km/h	100 kg
nerdjajuci	✓
Statički Nosivost	200 kg
Temperaturni opseg (Minimalno)	-20 °C
Opseg temperature (maksimalni)	60 °C
Sveukupna visina	162 mm

## TOCAK

Materijal za telo	polipropilen
materijal omotaca	Termoplastična guma
Nošenje	precizini kuglicni lezaj, nerdjajuci
stitnici omotaca	Sa threadguard
Prečnik	125 mm
Širina omotac	30 mm
Teškoća gazećeg omotac (A)	87 Šora A

## KUCISTE

Materijal	poliamid
oblik viljuska	Zatvoreno
okretni lezaj	Dve trke za loptu, Ojacano ili nerdjajuci
ofset	40 mm
Otpor okretanju	205 mm

## PRILAGOĐAVANJE

Tip uklapanja	stablo, okrugla
Prečnik sraf	22 mm
Dužina sraf	40 mm

## DODATNE INFORMACIJE

Dizajniran za sledeću velicina palete: sirina trake: pribl: 2,75 mm, sirina zleba: pribl. 5,7 mm, dubina zleba: > 10 mm.

# GALEA STAINLESS

5085PJC125R05-22X40

EAN 4031582336527



BETTER MOBILITY. BETTER LIFE.

## TEHNIČKI CRTEŽI

