

PURETECH AIR

DQR400X100-Ø25 HL74 4PR

EAN 4031582318203



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

Body material	Sheet Steel
Tread hardness	soft
Tread material	Pneumatic tyre, block profile
Bearing	Roller bearing
Threadguards	Without threadguard
Diameter	400 mm
Tread width	100 mm
Axle hole diameter	25 mm
Hub length	74 mm
Hardness of tread (A)	55 Shore A

PERFORMANCE

Roll performance	● ○ ○ ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Puretech air
Type	Wheel
Load capacity at 3 km/h	200 kg
Load capacity Static	400 kg
Overall weight	2.44 kg

PURETECH AIR

DQR400X100-Ø25 HL74 4PR

EAN 4031582318203



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

